




Tank Dimensions (mm)







Inlet Diameters


Ø	(mm)	
DN 70	+0.2 ø75 - 1.0	
DN 100	+0.3 ø110 -1.0	Ø
DN 150	+0.4 ø160 -1.5	

Connections

- 1. Inflow DN 150
- 2. Inflow DN 150
- 3. Inflow DN 100/150
- 4. Inflow DN 100/150
- 5. Inflow DN 150 (variable with 90° elbow)
- 6. Vent/Inflow DN 70
- 7. Vent/Inflow DN 70
- 8. Inflow/Hand membrane pump DN 40
- 9. Discharge flange DN 80

Note:

Rooms for sewage lifting stations must be large enough that a working area of at least 60 cm width or height is available around all parts which have to be operated or maintained. A pump sump should be provided for dewatering of the room itself.



Unit 8, Heron Business Park, Eastman Way, Hemel Hempstead, Hertfordshire, HP2 7FW Tel: 01442 211554, Fax: 01442 211553, Email: info@edincare.com,

Web: www.edincare.com

